

## HOW DO I DO 2-POINT SCALING ON A DP41-W?

### Set up procedure for Model DP41-W with 2-Point Calibration

Jumper Settings:

100mV S2: A,F,L,N,T

S6:Y

S1 "B" NOT INSTALLED UNIPOLAR [INP.3=0]

S1 "B" INSTALLED BIPOLAR [INP.3=1]

INSTALL S4-A,C for adjustable 1.5 to 11 Vdc Excitation output

INSTALL S3 A,C (default)

[L1 CNF] [LC CNF] [RDG.CNF] [IN.CNF] [DEC PT]

L1C.1=0 L2C.1=0 RDG.1=0 INP.1=0 FFFFFFFF.

L1C.2=0 L2C.2=0 RDG.2=1 INP.2=0

L1C.3=0 L2C.3=0 RDG.3=0 INP.3=0

L1C.4=0 L2C.4=0 RDG.4=1 INP.4=0

L1C.5=0 L2C.5=0 RDG.5=0 INP.5=0

L1C.6=0 L2C.6=0 RDG.6=0 INP.6=0

L1C.7=0 L2C.7=0 RDG.7=0 INP.7=1

L1C.8=0 INP.8=0

Set MAX CAP to 100,000 and MIN CAP to -10,000 to allow scaling

VERIFY ABOVE INITIAL CONDITIONS

PUT METER IN RUN MODE (PRESS RESET TWICE IF IN MENU MODE)

RECORD READING WITH \*\* NO LOAD ON TRANSDUCER\*\* INPUT1\_\_\_\_\_

RECORD READING WITH \*\* KNOWN LOAD ON TRANSDUCER\*\* INPUT2\_\_\_\_\_

Note: READ1 and READ2 below should include all significant digits

Example: enter 5000 for READ2 if final display is 500.0

READING DESIRED WITH NO LOAD (usually 000000) READ1\_\_\_\_\_

READING DESIRED WITH KNOWN LOAD READ2\_\_\_\_\_

PRESS MENU UNTIL "IN CNF" APPEARS PRESS MIN UNTIL "INP.5=0" APPEARS

PRESS MAX "INP.5=1"

PRESS MENU "IN.SC.OF" APPEARS

PRESS MIN -- <INPUT1> PRESS MIN -- ENTER INPUT 1 FROM ABOVE

PRESS MENU -- <READ1> PRESS MIN -- ENTER READ 1 (DESIRED LOW READING)

PRESS MIN -- <INPUT2> PRESS MIN -- ENTER INPUT 2 FROM ABOVE

PRESS MENU -- <READ2> PRESS MIN -- ENTER READ 2 (DESIRED HIGH READING)

PRESS MENU -- PRESS MIN PLACE DECIMAL POINT WITH MAX BUTTON -- PRESS MENU

PRESS RESET TWICE METER SHOULD NOW BE CALIBRATED

-----  
1. WHEN PROGRAMMING, PRESSING [RESET] ONCE WILL BACK UP ONE MENU

PRESSING [RESET] TWICE WILL RETURN TO RUN MODE

2. "IN CNF" INP.5 DETERMINES IF RAW DATA OR SCALED DATA IS SENT TO THE DISPLAY.

IN.SC.OF IS WHERE SCALING DATA IS INPUT. EVERY TIME THAT YOU ACTIVATE THIS MENU YOU MUST INPUT DATA.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters